

Waverly Collection
 Waverly 1 Light Wall Sconce NBR
 45745NBR (Natural Brass)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____



Ordering Information

| | |
|--------------------|--------------------|
| Product ID | 45745NBR |
| Finish | Natural Brass |
| Available Finishes | CLP, NBR |
| Collection | Waverly Collection |

Dimensions

| | |
|------------------------------------|----------|
| Extension | 9.25" |
| Height from center of Wall opening | 7.00" |
| Base Backplate | 7.00 DIA |
| Weight | 3.00 LBS |

Specifications

| | |
|----------------------|--------------|
| Material | Steel |
| Diffuser Description | Clear Seeded |

Electrical

| | |
|---------|-------|
| Voltage | 120 V |
|---------|-------|

Qualifications

| | |
|--------------|--------------------------|
| Safety Rated | Damp |
| Warranty | www.kichler.com/warranty |

Installation

| | |
|--------------------------|-----|
| Install Glass Up or Down | Yes |
|--------------------------|-----|

Primary Lamping

| | |
|------------------------|--------------|
| Light Source | Incandescent |
| Lamp Included | Not Included |
| # of Bulbs/LED Modules | 1 |
| Socket Wire | 150 |
| Socket Type | Medium |
| Lamp Type | A19 |

Dimensions

| | |
|--------|--------|
| Height | 11.50" |
| Width | 7.00" |

Alternate Lamps

| Lamp Included | Bulb Listing | Light Source | Max Wattage/Range | Bulb Product ID | Dimming |
|---------------|--------------|--------------|-------------------|-----------------|---------|
| No | Alternate | INCA | 60W | 4071CLR | |