

Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs are Circuit Protection Molded Case Circuit Breakers. 1-Pole circuit breaker type BQ. Rated 120V (015A) (AIR 10 kA). Special features: Load side lugs are included.



Number of poles	1
Suitability for operation	Electrical Distribution

### Electricity

Continuous current rated value	15 A
--------------------------------	------

### Model

Product brand name	SIEMENS
Type of electrical connection	BOLT-ON

### Mechanical Design

Depth [in]	4 in
Design of the product	BQ
Height [in]	1 in
Width [in]	3 in

### General product approval

Standard	UL 489
<b>last modified:</b>	03/08/2020