



GE
Lighting

35540 - GE LED MR16

LED5.5DMR1682735

- ☞ The Value 12 Volt AC/DC MR16 is an Energy-efficient LED lamps.
- ☞ Long life
- ☞ Energy Star Rated
- ☞ Flood 35° beam
- ☞ White

Product Photo



GENERAL CHARACTERISTICS

Base Description	GU5.3
Base Type	Plug-in
Dimmable	Yes
Lamp Type	LED-MR
Primary Application	Track & Recessed
Product Color	White
Product Technology	LED
Rated Life (Hours)	25000 h
Dimmable / Non-Dimmable	Yes
10 Digit U	4316835540
Lamp Count	1
Life in Years	22.8 yr
Replacement Watts	35 W
Requested Structure	Carton
Estimated Energy Cost per Year	0.66
Base	GU5.3
Bulb Shape	MR16

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	1000 cd
Lumens per Watt (Efficacy)	73 lm
Nominal Initial Lumen per Watt	73
Rated Beam Spread	35 deg
Initial Lumens-nominal	400 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	35540
Description	LED5.5DMR1682735
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168355407
Standard Package GTIN	10043168355404
No Of Items Per Sales Unit	
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	043168355407
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168355407
Standard Package GTIN	00043168355407
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168355407

DIMENSIONS

Bulb Max Overall Length-MOL	1.88 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	12 V
Input Voltage [nom]	12 V
Rated power (Watts)	5.5 W

CAUTIONS & WARNINGS

Caution

Risk of Electric Shock

Do not use where directly exposed to water

Not for use in totally enclosed luminaires

For use only with approved Class 2 transformers /drivers

Oct 12, 2017 6:39:51 AM For additional information, visit www.gelighting.com