



S9823

4W CFC/LED/27K/CL/120V
 Discontinued - 4 watt CA11 LED; Clear; Candelabra base;
 2700K; 340 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures
- Shatterproof option available on request



S9823

When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9823	045923098239	120	4	40W	>0.70	CA11	Candelabra

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens
E12	4W CFC/LED/27K/CL/120V	Dimmable	Compatible dimmers for S9823	Clear	4-11/16"	1-3/8"	340

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
15000	2700	Warm White	80	360	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box

RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty	Status	Suggested Substitute
Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	3 Year Limited	Discontinued	S9923



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

