



A-Shape LED

22A21/LED/827 3WAY ND 120V 6/1

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.


Product data

General Information		Warm Up Time To 60% Light (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]		0.5 s
Nominal Lifetime (Nom)	10000 h	Power Factor (Nom)	0.7
Switching Cycle	50000X	Voltage (Nom)	120 V
Technical Type	22-150W	Temperature	
Light Technical		T-Case Maximum (Nom)	100 °C
Color Code	827 [CCT of 2700K]	Controls and Dimming	
Initial lumen (Nom)	2200 lm	Dimmable	No
Luminous Flux (Rated) (Nom)	2200 lm	Mechanical and Housing	
Color Designation	Warm White (WW)	Bulb Finish	Frosted (FR)
Correlated Color Temperature (Nom)	2700 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	100 lm/W	Suitable For Accent Lighting	No
Color Consistency	ANSI	Product Data	
Color Rendering Index (Nom)	80	Order product name	22A21/LED/827 3WAY ND 120V 6/1
LLMF At End Of Nominal Lifetime (Nom)	70 %	EAN/UPC - Product	046677465155
Operating and Electrical		Order code	465153
Input Frequency	60 Hz	Numerator - Quantity Per Pack	1
Power (Rated) (Nom)	22 W	Numerator - Packs per outer box	6
Lamp Current (Nom)	220 mA	Material Nr. (12NC)	929001258404
Wattage Equivalent	150 W		
Starting Time (Nom)	0.5 s		

A-Shape LED

Net Weight (Piece) 0.155 kg



Dimensional drawing



Bulb 120V 22W-150W 2200lm 2700K E26d ND

Product	D	C
22A21/LED/827 3WAY ND 120V 6/1	71.1 mm	134.6 mm

Photometric data



General Uniform Lighting
 Catalog Photometric 4.5 Philips Lighting B.V. Page 171

