



## Description

Venture Lighting's LED Retrofit lamps are the ideal upgrade solution to traditional HID lamp technologies. Venture's LED Retrofit lamps are a simple energy saving solution for providing significant maintenance savings. The integrated driver design is an ideal upgrade from traditional technologies.

## Features & Benefits

- Replaces MH or HPS up to 175W\*
- Replaces CFL up to 85W\*
- 5 year warranty
- Universal burn position
- Easy installation
- Reduced maintenance costs
- *\*Note: It is the customer's responsibility to verify that the lamp compartment meets the minimum required lamp compartment dimension of 8" diameter by 11" long.*

## Applications

- Post top
- Wall pack
- Area Lighting
- Flood lighting
- Garage lighting
- General illumination

## Notes

- The use of an external surge protection device is recommended.
- Operating temp. range between -40°F and 122°F (-40°C and 50°C).
- Suitable for use in dry and damp environments.
- Suitable for use in portable, surface mounted and ceiling luminaires.
- Suitable for use in open and enclosed luminaires with minimum lamp compartment dimensions of 8 inch diameter x 11 inch deep.
- Do not use where exposed to water or outdoors without an appropriate enclosed luminaire.
- Lamps have clear polycarbonate cover lenses

## VL1-OR027-40E39-AE00

### Product Performance

Input Power (W)	27
Bare Lamp Lumens	3240
DLC Rated Lumens	2500
Lumens/Watt (Bare Lamp)	120
Beam Angle (°)	360
Correlated Color Temperature (CCT)	4000K
Color Rendering Index (CRI)	80
Life Hours	50000
Minimum Lamp Compartment Size	6" Dia by 8.5" long
Dimming	No
Operating Temperature Range	-40°F to 122°F (-40°C to 50°C)

### Physical Characteristics

Base Type	Mogul, (E39)
Overall Length A	8.07" (205mm)
Diameter B	3.66" (93mm)
Weight	1.6 lbs (726 g)

### Electrical Characteristics

Input Voltage Range	100V-277V; 50/60Hz
Driver	Internal within lamp
Power Factor	>0.90
THD	<20%

### Regulatory Qualifications



- cULus Listed
- cULus Classified – Certified to UL 1598C
- DLC Qualified - Model# VL1-OR027-40E39-AE00

### Accessories

- SP12714 – 120-277V Surge Protector



# Venture 27W LED Retrofit Lamp



Easy to install - bypass ballast and provide voltage directly to lamp

(800) 451-2606  
Fax: (800) 451-2605  
2451 Enterprise Parkway East  
Twinsburg, Ohio 44087 USA  
E-mail: [venture@adlt.com](mailto:venture@adlt.com)  
[VentureLighting.com](http://VentureLighting.com)

