



S9815

15.5A21/LED/2700K/1600L/120V/D
 15.5 watt; A21 LED; Frosted; 2700K; Medium base; 220' beam spread; 120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable
- UL approved for totally enclosed fixtures
- ?Compatible Dimmers
 - Leviton 6674
 - Lutron MACL-153M
 - Lutron NTCL-250
 - Lutron PD-6WCL
 - Lutron SELV-300P



S9815

| Item Number | UPC | Voltage | Watts | Power Factor | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|--------------|------------|--------|-----------|
| S9815 | 045923098154 | 120 | 15.5 | 0.96 | A21 | Medium | E26 |

| Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|--------------------------------|-----------------------|---------|---------------|---------------|----------------|---------------------|-------------|
| 15.5A21/LED/2700K/1600L/120V/D | Dimmable | Frosted | 5 9/16" | 2 5/8" | 1600 | 25000 | 2700 |

| Color | CRI | Beam Spread Deg | Operating Temperature | Pack | Package Type | RoHS Compliant | UL or ETL Listed |
|------------|-----|-----------------|---|------|--------------|----------------|------------------|
| Warm White | 80 | 220 | Operating temperature: -20°C (-4°F) to a maximum of +45°C (113°F) | 24/6 | Box | Yes | Yes |

| UL Classification | Warranty |
|-----------------------------|--------------------------------|
| cULus - Damp Location Rated | 3 Year Limited |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

