

LED Indoor Reflector

LBR40/11/830/D

LED BR40 Lamp

- Dimmable down to 10%
- Lasts 10x longer than traditional incandescents
- Contains no mercury
- Not approved for use in enclosed fixtures



Item #	LBR40/11/830/D-46
Product Code	78932
UPC Code	751338002227
Watts	11.5
Volts	120
Lamp Shape	BR40
Base	E26 Medium
Beam Spread	103°
CRI	80
Color Temp	3000K
Initial Lumens	940
CBCP	340
Average Rated Life	25,000
Min. Start Temp	-20°C
MOL	6.5"
Equivalent Wattage	75
Warranty	5 years

Specifications are subject to change without prior notice.

