



S9720

15T8/LED/48-830/BP/120-277V
 15 watt T8 LED; Medium bi-pin base; 3000K; 50000 average rated hours; 1700 lumens



Features

- No ballast or external driver required
- Direct wire 120-277V line voltage*
- All glass tube
- -20°C (-4°F) to 45°C (113°F) - ambient operating temperature
- Long life: 50,000 hours
- cULus classified - Damp location
- 5 year warranty
- DLC listed

S9720

* Install only in non-shunted lampholders

Item Number	UPC	Voltage	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base
S9720	045923097201	120-277	15	25-32	T8	Medium Bi-Pin	G13

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15T8/LED/48-830/BP/120-277V	Non-Dimmable	Gloss White	48"	1.00"	1700	50000	3000

Color	CRI	Beam Spread Deg	Pack	DLC ID:	RoHS Compliant	UL or ETL Listed	UL Classification
Warm White	82	230	10	P3AEX5ZM; PP4RYCMN DLC Search	Yes	Yes	cULus - Damp Location Rated

Warranty							
5 Year Limited							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

