



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA1CL2  
7818105512644  
1STR CU 1-HOLE SHORT 1/4  
Active

**Web Use**  
BURNDY Product Line

Tongue Angle  
Length (in)  
Tongue Type  
Barrell Style  
Bolt Hole Size (in)  
Barrel Type  
Thickness  
B Length (in)  
Pad Width (in)  
Strip Length

**Dimensional**

Straight  
1.81  
Standard  
Chamfered,Skived  
0.27  
Standard  
0.10  
0.88  
0.68  
15/16

Number of Holes

**General**

1  
CU Compression Terminal Code  
Conductor, Beveled Entry, 1  
Hole/W/InspWindow,  
#1AWG(Code) 75(Navy), 600V-  
35kV, 1/4" Stud, Standard Barrel,  
Electro-Tin Plated

Product Description

**Conductor(s)**

Flex (Class G) Size - Range  
Flex (Class H) Size - Range  
Flex (Class I) Size - Range  
Copper Solid Size (Range)  
DLO Size (Range)  
Copper Stranded (Range)

N/A  
N/A  
N/A  
N/A  
N/A  
1 AWG

Type of Plating  
Bolt Hole Size  
Color Code  
Plated (Yes or No)  
Index Number  
Product Material

**Physical**

Tin - Electro Plated  
1/4  
Green  
Y  
375,11  
Copper

**Approvals / Certifications**

UL Listed  
CSA Certified  
ROHS Compatible  
UL Recognized  
CULUS  
Industry Standards

Y  
Y  
Compliant  
N  
N  
UL467

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175