

# LED LAMP

## SPECIFICATIONS

### Ideal For

Recessed Lighting

Warm White  
3000K

### Features

- Instant On To Full Brightness
- Suitable For Damp Locations
- Dimmable
- ETL Listed
- FCC Compliant
- 100% Mercury Free
- 2 Year Warranty
- Warm White

### Benefits

- Full Range Dimming
- Energy Efficient: Up to 88% less energy than standard incandescent
- No Ultraviolet - Safe for artwork
- Color Consistency
- Low Heat
- Durable
- Long Life



### Specifications

| Item Number         | Input Power (Watts)          | Incandescent Equiv. (Watts) | Input Line Voltage |
|---------------------|------------------------------|-----------------------------|--------------------|
| BR40/DM/2500/3K/LED | 30                           | 250                         | 120                |
| Base Type           | Lumens                       | Lumen Efficiency (LPW)      | CCT                |
| E26 (Medium)        | 2500                         | 83                          | 3000K              |
| CRI                 | Beam Angle                   | MOL                         | Diameter           |
| >80                 | 120°                         | 6.3"                        | 5"                 |
| Life Hours          | Minimum Starting Temperature |                             |                    |
| 25,000              | -13°F                        |                             |                    |