



\*max overall height

**Measurements:**

<u>Height</u>	<u>Width</u>	<u>Length</u>		
9.50"	28.00"	28.00"		
<u>Max OAH</u>	<u>Min OAH</u>			
51.50"	13.75"			
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>	
9.70 lb	4.96"	2.44"	4.96"	

**Lamping:**

LED PCB LED 2,600 Rated Lumens  
 5.00 33W PCB LED 3000 Color Temperature  
 33 total watt 90+ CRI  
 Dimmable : Standard Triac/Lutron® or Leviton® CL

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
12.79 lb	25.20"	7.87"	25.20"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209131378	Yes	

**Finish:**

Satin Nickel SN

**Glass:**

Satin White SW

**Material:**

Steel

**Certification:**

Dry Location

**Additional:**

PCB LED (Not Included)  
 Slope: 120