



\*max overall height

**Measurements:**

<u>Height</u>	<u>Width</u>	<u>Length</u>
19.75"	10.25"	22.75"
<u>Max OAH</u>	<u>Min OAH</u>	
30.75"	19.75"	

Hanging Weight

11.02 lb

**Lamping:**

LED GU24 LED	600 Rated Lumens
1.00 9W GU24 LED	3000 Color Temperature
9 total watt	90+ CRI
Dimmable : Electronic Low Voltage (ELV)	Input Voltage: 120

**Shipping:**

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
14.99 lb	12.40"	12.80"	20.28"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209129177	Yes	

**Finish:**

Polished Chrome PC

**Material:**

Steel

**Certification:**

Dry Location  
Energy Star  
ADA

**Additional:**

GU24 LED (Included)