



**Catalog#: ESBL2N4**


**WET LOCATION EMERGENCY LIGHT/EXIT SIGN COMBO UNIT WITH BATTERY BACK-UP**

**Category** Wet Location Exit Signs  
**Page** [E16](#) [17](#) (Exit & Emergency Lighting Catalog)

**Features:**

- Dual-Voltage Input 120/277VAC Operation
- ETL Listed for Wet Location
- Suitable for cold weather **with heater option**
- Long-lasting, Energy Saving LED Lamps
- Two fully adjustable 6V 5.4W T5 Wedge Based Waterproof Lamp Heads
- 90 Minutes Minimum Emergency Operation
- Injection Molded, 5VA Flame Retardant, Polycarbonate
- Fully Gasketed Corrosion-Resistant Enclosure
- High-Impact Clear Polycarbonate Lens
- Universal Mounting Plate
- Single Face wall surface mount only
- Easy Snap-out Chevrons Directional Indicators
- Sealed Push to Test Switch
- Grey housing, White faceplate
- Maintenance Free 4.8V NiCd Battery
- Fully automatic operation

**Line Drawings:**



**Certifications:**



CAT NO	Letters Color	Options
ESBL2N4	R (Red) G (Green)	HTR (Internal Heater)

