



SPECIFICATIONS

GENERAL:

- DIAMETER: 11"
- EXTENSION: 6"
- IN/OUT: INDOOR DAMP

MATERIALS:

- GLASS: FAUX ALABASTER GLASS
- REPLACEMENT GLASS: G7630

ELECTRICAL:

- F7630-53 / F7630-62:
2 MEDIUM BASE 60 WATT MAX
A19 LAMPS NOT INCLUDED 120 VOLTS

- F7631-53:
1 GU24 BASE 18 WATT MAX
BULB INCLUDED




MOUNTING:

- CEILING

FINISHES:

- SATIN NICKEL - 53 (SN)
- RUBBED BRONZE - 62 (RB)



Please contact your representative for more color options.