



BURNDY Catalog Number
UPC Number
Description
Status

TP108F
7818107106855
FORK- 12- 10 AWG- VINYL
Active

Web Use
BURNDY Product Line

Strip Length
Length (in)
Tongue Type
Thickness
B Length (in)

Dimensional

19/64
0.98
Fork
0.04
0.34

Max Voltage Rating

Electrical

600

Product Description

General

Insulated Brazed Fork Terminal,
Insulated Brazed Fork Terminal,
Smooth Entry, #12-#10, 600V, #6-
#8 Stud, Vinyl Insulated, Tin
Plated

Bulk Package

Other

BA10EF8

Type of Plating
Connector Type
Insulation Type
Plated (Yes or No)

Physical

Tin
Terminal - Fork
Vinyl
Y

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications

Y
Y
Compliant
N
N

Copper Solid Size (Range)
Copper Stranded (Range)

Conductor(s)

N/A
12 AWG-10 AWG

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175