



Now In: [Penn-Union Products](#) → [Mechanical Lugs & Splices](#) → [Aluminum Solderless Lugs](#) → [L2A - 2 Conductors - 1 Hole](#) → L2A-250 - Aluminum Solderless Lug



## L2A-250 - Aluminum Solderless Lug

One hole, front entrance

For two copper or aluminum conductors


Body fabricated from high strength aluminum alloy extrusion

Lug is 100% reusable using hex wrench

No special tools required

Maximum conductivity, compact design, light weight with ultimate strength

### Product Drawing:



[Click to expand.](#)

Electro-tin plated to assure minimum contact resistance and protection against corrosion when used with copper wire

For added protection apply Penn-Union Cual-Aid® to cable before installation

Conductor Type	Conductor Range
Aluminum or Copper	6 - 250 MCM

No. of Holes in Pad:	1
No. of Conductors:	2

Additional Details	
Screw Size:	Socket
UL Listing:	486B LISTED AL9CU
CSA Listing:	Yes

Approximate Dimensions	
Fig. No.:	2
B (in.):	1 9/16
C (in.):	7/8
D (in.):	13/32

### PRODUCT QUICK SEARCH:

[Penn Union Search:](#)

[Competitor Search:](#)



<b>H (in.):</b>	1 3/16
<b>L (in.):</b>	2 9/16
<b>T (in.):</b>	1/4
<b>W (in.):</b>	1 41/64
<b>Torque (in./lb.):</b>	275



© 2008 Penn-Union Corp. · 229 Waterford Street · Edinboro, PA 16412  
Phone: 814-734-1631 · Fax: 814-734-4946 · info@penn-union.com

Designed & Developed by O-Web Technologies, Ltd.