



S9872

2.5T6/LED/CL/27K/E12/120V
2.5 watt T6 LED; Clear; Candelabra base; 2700K; 200 lumens;
120 volts

Features

- Solid State LED lighting
- Long life
- Dimmable
- Approved for enclosed fixtures



S9872

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9872	045923098727	120	2.5	15W	T6	Candelabra	E12
Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
2.5T6/LED/CL/27K/E12/120V	Dimmable	Compatible dimmers for S9872	Clear	3 3/16"	0.75"	200	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification
2700	Warm White	80	360	CD/1	Yes	Yes	cULus - Wet Location Rated
Warranty							
3 Year Limited							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

