



Stranded Wire Grounding Tail; 12 AWG, 7-3/4 in. tail w/ #10 fork & #10 ring and ground screw (Bag of 25)



Product Resources

[IDEAL Connector UL Listed Wire Combinations](#)
(PDF | 378K)

Features

- Six Inch stranded wire pigtail
- Ideal for Grounding and Bonding Applications
- Stranded pigtail lead wires are convenient for device grounding applications
- Grounding screw offers a unique thread-forming, hole-finding feature plus combination 5/16 in. hex, #2 Phillips, 1/4 in. slotted and #2 Robertson head
- Ultra-flexible lead wire tucks easily into box
- Heavy-duty fork terminal attaches easily to grounding screw
- Reduces time required for device bonding
- Ensures compliance with NEC standards
- UL and CUL listed

Models

Description	Catalog #
Stranded Wire Grounding Tail; 12 AWG, 7-3/4 in. tail w/ #10 fork & #10 ring and ground screw (Bag of 25)	30-3184

©2014 IDEAL INDUSTRIES, INC. All rights reserved.