




Item #
F852L-HBZ
 Product Family Name:
Alva
 Category:
INTERIOR FAN
 Certification
3064964
 Patents:
U.S. Patent(s): Pending
 Notes:

UPC Code:
706411056383
 Finish:
Heirloom Bronze
 Category Type:
Ceiling Fan



Image File Name: **F852L-HBZ.jpg**



MEASUREMENTS

Blade Finish:				Reversible Blades:	No
Blade Material:				Slope:	Yes
WOOD				Hanging Weight:	16.56
Blade Sweep:	No. of Blades:	Blade Pitch:			
56"	5	14 DEGREES			
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:		
6	0.75				
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade (Dim B)	Lead Wire:	Motor Size:		
20.5	11.0	80"	DC 120X15MM		

	Low	Low/Med.	Medium	Med/High	High
RPM:	70				144
Amps:	0.07				0.45
Watts:	4.19				32.56
CFM:	3304.0				7045.0
CFM/Watts:	788.54				216.37

LAMPING

No. of Bulbs:	Light Type:			
3	LED, FERRO			
Max Bulb Wattage:	Socket:			
6	LED, FERRO			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight:
Yes	Yes		30000	No
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	2700	90	1586.0	1301.0

GLASS

Description:	Material:
Part No.:	Quantity:
Width:	Height:
	Length:



FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
No	Yes	No
Reversible:	Included Remote Control:	Included Wall Control:
Yes	RC500	
	Compatible Remote Control(s):	Compatible Wall Control(s):



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
12.0	11.25	26.75	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
19.93	2.09	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		1	1

LED

LED



ETL Intertek