



Description	GLASS BALLAST BYPASS DLC V4.1 T8 4FT 18W-2200LM 4000K NON-DIM 80CRI 120-277V
Ordering Code	09397
UNSPSC Code	39101628

Specifications

Voltage Rating	120~277
Voltage Type	AC
Watts	18
mA	155
Lumens per Watt	122.22
Base Type	G13
Bulb Type	T8
MOL in/mm	47.78/1213.60
MOD in/mm	1.02/26.00
Lumens	2200
CT deg K	4000
CRI	80+
Beam Angle	210°
Rated Life	50000
Special Desc	Not for Emergency Lighting
Ambient Operating Temp Range	-20° C (-4° F) to 45° C (113° F)
Approvals	cULus, DLC, NSF

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335