

High-Power LED PAR

LP30/10/27K/D

10.5 Watt LED PAR30 Lamp



- Dimmable down to 10%
- Advanced Optics & Thermal Management
- Contains no mercury

Item #	LP30/10/27K/D-46
Product Code	70926
UPC Code	751338002975
Watts	10.5
Volts	120
Lamp Shape	PAR30
Base	E26 Medium
Beam Spread	40°
CRI	80
Color Temp	2700K
Initial Lumens	810
Average Rated Life	25,000
MOL	3.625"
Equivalent Wattage	75
Warranty	5 years

Specifications are subject to change without prior notice.

Not suitable for use in enclosed fixtures

