

**Features**

- Fully self-contained emergency light that can be recessed into walls or ceilings.
- Compact, universal (wall or ceiling) backbox is provided with fully adjustable mounting hardware to suit virtually any application.
- Universal backbox can be pre-shipped for pre-installation at job-site.
- Compact rotating 4" door.
- Superflux 25 watt lamps are equivalent to the light output of 35 watt MR11 lamps.
- UL listed 90 minute run-time.
- Can be painted or wall-papered to seamlessly blend with architecture.
- Soft-close doors.
- Optional infra-red hand-held remote control testing.
- Modular assembly and quick connector wiring for easy installation.
- Uni-directional deflecting drive band motor (patent pending).
- Solid state microprocessor controlled circuitry.
- Line latch prevents unnecessary discharge of battery during installation.
- Brownout sensing ensures emergency operation during periods of low line voltage.
- Battery LVCO.
- Fully automatic operation.
- Battery diagnostics comes standard on all units.
- Soft start lamp circuit.
- 120/277 VAC field-selectable inputs.

**Construction**




- Textured, white powder coated, die-cast zinc frame and door.
- Spring latch lamp holders.
- No external mounting hardware.



Mini Genie Closed



### Ordering Information



#### Series

- MIGN-25** = (2) 25W Superflux MR11 Lamps
- MIGN-20** = (2) 20W Superflux MR11 Lamps

#### Battery

- LC** = Lead Calcium
- NC** = NiCad

#### Mounting

- UI** = Universal Backbox included
- SM** = Surface Mount
- UP** = Pre-ship Backbox

#### Options

- CP** = Chicago Plenum Listed
- DL** = Damp Location
- NY** = New York City Approved
- SQ** = Square Trim
- TD** = Time Delay
- SD** = Full Self-Diagnostics
- CC** = Custom Color
- TLRT** = Infra-red remote control (order separately)

#### Overall Size

- **Front Panel:** 7" x 7"
- **Rotating Door:** 4" x 4"

#### Backbox Size

- 5.25" x 14.375"

#### Rough-in Size

- 5.375" x 5.375"

#### Weight

12 lb

#### Approvals

- UL924
- NY City approved calendar #48850
- NFPA 101 Life Safety Code
- NFPA 70-NEC
- OSHA

#### Temperature Rating

- **LC:** From 45°F to 85°F
- **NC:** From 32°F to 102°F

#### Warranty

- Isolite offers a 3-year limited warranty. For further details, refer to General Warranty and Obligations in the Isolite manual or on our website. Lamps not warranted.

