



PRODUCT SEARCH

[> SUPP](#)
[> DIST](#)[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &
Miscellaneous](#)**Name:**

Strength - 85 lbs. 378 N Length - 2200 ft 670 m

Cat #:

604

UPC #:

23368

Spec:**Description:**

Strong, lightweight nylon.

- 595 - Center feed for fast payout without tangling. Use with Mighty Mouser® blow gun.
- 604, 605, 606 and 607 - Specially wound to payout fast from outside without tangles.
- Mildew resistant, can be pulled into the run with the wire to provide a means to add wires later.