

Vassar Collection  
 52 Inch Vassar LED Fan OZ  
 330002OZ (Olde Bronze)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_

**Product Information**

Product ID	330002OZ
Finish	Olde Bronze
Blade Finish	Cherry/Walnut
Collection	Vassar Collection

**Airflow, Power and Efficiency**

Speed	RPM	CFM	CFM/ Watt	Amps	Watts
High	178	5041	91	.47	55
Med	128	3415	117	.4	29
Low	83	2214	188	.29	12

**Specifications**

Number of Blades	3
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	52"
Blades Reversible	No
Blade Material	Wood
Optional Blades Available	No
Downrod 1	1.00 OD X 4.00

3 Speed Wall Control Ltd Function - In project applications using multiple ceiling fans, alternative remote controls may be required. Please contact Kichler Advanced Product Solutions at 844-542-4537 to confirm your project requirements.


Primary Control System	
Remote Included	No
Wall Control Included	Yes
Low Ceiling Adaptable	No
Lead Wire Length	78.00"
Motor Size	153MM X 17MM
Motor Type	AC INDUCTION

**Downlight**

Downlight Included	Yes
Light Source	LED
Downlight Bulb Included	Included
Downlight Bulb Type	LED
# of Bulbs/LED Modules	1



**Dimensions**



Downrod	A	B	C	D
1.00 OD X 4.00	15.00	11.00	8.75	6.25

**Available Finishes**

Finish	Fixture	Glass	Blade 1	Blade 2
Brushed Nickel	330002NI	ETCHED CASED OPAL	SILVER	WALNUT

**Kichler**  
 7711 East Pleasant Valley Road  
 Cleveland, Ohio 44131-8010  
 Toll free: 866.558.5706 or kichler.com

**Notes:**  
 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.  
 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

**KICHLER.**

# Vassar Collection

## 52 Inch Vassar LED Fan OZ

330002OZ (Olde Bronze)

Project Name: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Qty: \_\_\_\_\_  
 Comments: \_\_\_\_\_

Finish	Fixture	Glass	Blade 1	Blade 2
Olde Bronze	330002OZ	ETCHED CASED OPAL	CHERRY	WALNUT
White	330002WH	ETCHED CASED OPAL	WHITE	SILVER

Watts	55/29/12
Initial Lumens	1600
Glass Description	Etched Cased Opal
Optional Light Kit Available	No
Efficacy (LMIW)	94
Kelvin Temperature	3000 K
Color Rendering Index	80

### Safety Listings & Certifications

Safety Rated	Dry
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

### Installation

Installation requirements	The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked ""For Fan Support""
Electrical Requirements	120V 60Hz AC
Hanging Weight	17.20 LBS
Minimum Distance Between Bottom Of Fan Blade To Floor	7 feet

**Notes:**

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.