



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton's Type BR Non-EUSERC Meter Breaker,

**MBT48B150BTS**

**UPC:**782116894529

### Dimensions:

- **Height:** 25.5 IN
- **Length:** 4.94 IN
- **Width:** 14.44 IN

**Weight:**33 LB

### Warranties:

- 10 year

### Specifications:

- **Type:** All-in-ones
- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Overhead/underground
- **Ground:** #6-350 kcmil
- **Interrupt Rating:** 22 kAIC
- **Main Circuit Breaker:** CSR2150
- **Mounting:** Surface mounting
- **Number Of Circuits:** 8
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Number Of Spaces:** 4
- **Phase:** Single-phase
- **Security:** Ringless
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - MBT48B150BTS](#)
- [Dimensional Drawing - METER BREAKER](#)



## TRAILER PANEL

### **Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.