

CRAFTMADE

Tempo - TMP52BNK5

52" Ceiling Fan with Blades and LED Light Kit

Finish:



Tempo 52" ceiling fan is a statement of refined Modern design. LED down lighting and up lighting are incorporated in this knockout.


- Heavy-Duty, 3-Speed Reversible Motor
- 6" Downrod (Included)
- Reversible Silver/Maple Blades (Included)
- Integrated Uplight and Downlight (1-16 Watt LED 3000K Dimmable Bulb Included)
- ICS Remote & Wall Controls (Included)
- Optional Blank Light Lens Cover (Included)
- Remote On/Off or Dimming

Specs

Blade Sweep Opt (in.)	52
Blades	5
Blade Pitch (°)	13
Motor Size (MM)	172 x 17
Amps at High Speed	0.64
Airflow (CFM)	5304
Watts (Hi Speed)	72.90
Efficiency (CFM/Watt)	73
Shipping Weight (lbs.)	23.30
Carton Size (CU FT)	2.48
CRI	80
Kelvins	3000
Lumens	1415
Bulb Wattage	16

Dimensions

A (in.):	15.80
B (in.):	12.62
C (in.):	12.39
D:	6.30
H (in.):	6.30
H (in.):	12.39
Downrod Length (in.)	6



Guide

Tempo - TMP52BNK5



[Installation Guide](#)