

## VS17402-HTBZ: 2 - Light Vanity Fixture



### Dimensions:

Length: 14"      Extends: 7"  
 Height: 8 5/8"      Wire: 8"  
 Weight: 3.52 lbs.      Mounting Proc.: Mounting Strap  
 Connection: Mounted To Box

### Bulbs:

2 - Medium A19 100w Max. 120v - Not included

### Features:

- Fixture may be mounted in the up or down position

### Material List:

1 Body - Steel - Heritage Bronze

### Safety Listing:

Safety Listed for Damp Locations  
 Safety Listed for Damp Locations

### Instruction Sheets:

English (VS17401)

Collection: Perry

UPC #:014817408485

Finish: Heritage Bronze (HTBZ)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	White Opal Etched	2				5 1/4	4 3/8				

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	4 5/8	8 1/4	1 1/8		2 1/4	2 1/4

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	VS17402-HTBZ	1	014817408485	9	16.5	11	0.945	4.8	150	Yes

NJ Pallet		72		48	40	71	78.889	345.6		No
NV Pallet		60		48	40	71	78.889	300		No