

**PHILIPS
HADCO**

Landscape

LED flood light

WAM1D/WBM1D



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Philips Hadco wall washer flood light line-voltage landscape luminaire has interchangeable LED color temperature between 3K and 4K CCT. This adjustable luminaire also has the ability to switch between 5 preset light outputs.

Ordering guide

Example: WAM1DFG2-A

Series	Lens	Generation	Finish
<input type="text"/>	<input type="checkbox"/>	<input type="text"/>	<input type="checkbox"/>
WAM1D Aluminum Flood light with shroud WBM1D Aluminum Flood light without shroud	F Frosted Lens C Clear Lens	G2 Generation 2	A Black B White H Bronze

Features

- 120-277 Volt
- 1/2" NPS fitter
- >70 CRI

Housing

A380 die-cast aluminum, able to remove shroud from housing with 2 screws. Adjustable knuckle stem provides range of rotation, prevents fixture from pointing past vertical. Vibration locking teeth secured by black oxide stainless steel screw. Driver mounts directly to housing for thermal management. All gaskets are 100% molded silicone.

Shroud

Gasketed, cast aluminum available (WAM1D).

Finish

Thermoset powder coated in black, white, or bronze.

LED

- 50,000 hours life at 25°C ambient temperature and 70% lumen maintenance.
- Color temp (CCT): Warm white (3000K) is standard. Cool white (4000K) is optional and is switchable at the fixture.

Controls

Class 2 driver with AOC and 0-10V dimming. Design allows easy-access to integral switch with 5 preset light outputs, see lumen matrix. Remove lens cap with [2] screws and simply adjust the slider switch by hand.

Optics

Clear or frosted tempered glass. 150° LED spread (equivalent to wide flood).

Electrical

10.6W (on high setting)
 Input voltage range (VAC): 120-277V. Pre-wired with #18 AWG black, white and ground wire for ease of connection. Also has #18 AWG grey and violet for 0-10V Analog Class 2 dimming, capped off to help prevent cross wiring with line- voltage wires.

Labels

ETL and cETL listed.

Warranty

5 year limited warranty.




WAM1D/WBM1D LED flood light

Aluminum, line voltage

Lumen matrix

Switch Settings (Nominal)	Typical Wattage Consumption	WAM1 Warm Clear Lens	WAM1 Cool Clear Lens	WAM1 Warm Frosted Lens	WAM1 Cool Frosted Lens	WBM1 Warm Clear Lens	WBM1 Cool Clear Lens	WBM1 Warm Frosted Lens	WBM1 Cool Frosted Lens
100% (5)	10.6	997	926	805	760	1187	1195	964	974
80% (4)	8.0	779	724	629	594	927	934	753	761
60% (3)	6.1	600	557	484	457	714	719	580	586
40% (2)	4.3	418	388	338	319	498	501	404	408
20% (1)	2.7	223	207	180	170	265	267	216	218

Dimensions and finishes



© 2017 Philips Lighting Holding B.V. All rights reserved.
 Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.
philips.com/luminaires



Philips Lighting North America Corporation
 200 Franklin Square Drive, Somerset, NJ 08873
 Tel. 855-486-2216

Philips Lighting Canada Ltd.
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3
 Tel. 800-668-9008