








Catalog Number: U2756-X-5T9
Item Description: 100A 5T RL MD LVR 6P CTR
UPC Code: 784572135994

Brand Name: Milbank
Type: Ringless Meter Socket
Application: Meter Socket
Standard: UL Listed
Voltage Rating: 600 Volts Alternating Current
Amperage Rating: 100 Continuous Ampere
Phase: 1 Phase
Frequency Rating: 60 Hertz
Number Of Cutouts: 0
Cutout Size: No Main Breaker
Cable Entry: Overhead and Underground
Terminal: 3/8 Inch Stud Line Side and Single Lay
in Load Side
Insulation: Glass Polyester
Mounting: Surface Mount
Enclosure: Type 3R, G90 Galvanized Steel with
Powder Coat Finish
Number Receptacles: 0



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	6	STD. MNTG. EMBOSS
B	1	½, ¾, 1 CONC. K.O.
C	14	¾, 1, 1¼, 1½ CONC. K.O.
D	2	2, 2½, 3 CONC. K.O.



Version:

1

All dimensions are +/- 1/16".
 Drawing views are not to scale.
 Utility requirements for this equipment may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.