

Rigid Conduit Bodies with Cover and Gasket

Threaded LR Type

Features

- Threaded LR type with cover and gasket
- NPT tapered hubs
- Suitable for use in concrete
- Suitable for use in wet locations

Applications


- Provides access to conductors for pulling, splicing and maintenance

Standard Material

- Copper free aluminum die cast
- Cover - Stamped steel
- Gasket - Neoprene rubber

Standard Finish

- Powder coat



Catalog Number	UPC	Size	Wire Size		Unit Carton	Ship Case	Weight/Case	Inches		
			Max. Number	Max. Size				A	B	C
LR1CG	21241	1/2"	1	6 AWG	10	100	36	4.295	1.37	2.03
LR2CG	21251	3/4"	2	6 AWG	10	50	28	5.09	1.625	2.33
LR3CG	21261	1"	3	6 AWG	5	25	17	5.915	1.90	2.65
LR4CG	21271	1-1/4"	3	2 AWG	2	10	15	7.894	2.77	3.385
LR5CG	21281	1-1/2"	3	2 AWG	2	10	18	7.894	2.77	3.385
LR6CG	21291	2"	3	2/O AWG	1	5	14	10.134	3.335	3.81
LR7CG	21301	2-1/2"	3	4/O AWG	---	1	7	13	4.063	5.709
LR8CG	21311	3"	3	250 MCM	---	1	7	12.75	4.682	5.506
LR9CG	21321	3-1/2"	3	350 MCM	---	1	10	15.50	5.452	6.171
LR10CG	21331	4"	4	350 MCM	---	1	10	15.50	5.452	6.171