

2X2 / 2X4 FLAT PANEL LAMP A Series

FEATURES

WATTAGE: 30-45W
 125 LPW
 INPUT VOLTAGE: 100V-277V
 COLOR RENDERING INDEX (CRI): ≥ 80
 50,000 Hour Life
 POWER FACTOR: 0.9 Nominal
 Dimmable 0-10
 WARRANTY: 50,000 hours
 IC Rated
 Suitable for Damp Location

SPECIFICATIONS		2X2	2X4
GENERAL PERFORMANCE	POWER CONSUMPTION	30W	45W
	LUMENS DELIVERED	3750	5600
	CRI	≥ 83	≥ 83
	COLOR TEMPERATURE (CCT)	4000K, 5000K	4000K, 5000K
	LUMEN MAINTENANCE	50,000 HOURS	50,000 HOURS
ELECTRICAL	POWER FACTOR	≥ 0.9	≥ 0.9
	INPUT VOLTAGE	120V-277V	120V-277V
	LENS	FROSTED	FROSTED
CERTIFICATION	CERTIFICATION	UL, DLC, CCEA	UL, DLC, CCEA
	WARRANTY	50,000 HOURS	50,000 HOURS

ORDERING

ITEM	MODEL	WATTS	LENGTH	CCT	WARRANTY
50248-AL	FP30W35K2X2/4.0-A	30	2X2	3500K	50,000 HOURS
50249-AL	FP30W40K2X2/4.0-A	30	2X2	4000K	50,000 HOURS
50251-AL	FP45W35K2X4/4.0-A	45	2X4	3500K	50,000 HOURS
50252-AL	FP45W40K2x4/4.0-A	45	2X4	4000K	50,000 HOURS



ARLEE LIGHTING