



- ◆ Made In **U.S.A.**
 - ◆ 1/2" Universal Shank
 - ◆ Milled Teeth
 - ◆ Matrix II Cutting Edge
 - ◆ Tooth Hardness Rc 65-67
 - ◆ 8% Cobalt
 - ◆ Vacuum Heat Treatment
 - ◆ Long Life
- ◆ Shock Resistant Teeth
 - ◆ High Edge Hardness
 - ◆ High Heat Resistance
 - ◆ High Wear Resistance
 - ◆ Greater Rigidity
 - ◆ Resists Tooth Strippage
 - ◆ Accepts Higher Feed Pressure.

Made In



All Purpose Reciprocating Blades - Bi-Metal



Part #	Blade Length	Teeth Per Inch	Description	Width / Length	Pack QTY.	List	Bulk (50 Pcs.) Part #	List
RB636W	6"	6T	Wood & Nail Slope	3/4" x 6" x .050	5	\$3.06	BU-RB636W	\$3.01
RB656WS	6"	6T	Wood & Nail Scroll	3/4" x 6" x .050	5	\$3.17	BU-RB656WS	\$3.12
RB956W	9"	6T	Wood & Nail	3/4" x 9" x .050	5	\$4.31	BU-RB956W	\$4.06
RB125W	12"	6T	Wood & Nail	3/4" x 12" x .050	5	\$5.41	BU-RB125W	\$5.36
RB414M	4"	14T	Metal	3/4" x 4" x .035	5	\$1.89	BU-RB414M	\$1.81
RB418M	4"	18T	Metal	3/4" x 4" x .035	5	\$1.89	BU-RB418M	\$1.81
RB424M	4"	24T	Metal	3/4" x 4" x .035	5	\$1.89	BU-RB424M	\$1.81
RB610HDM	6"	10T	Metal	3/4" x 6" x .035	5	\$2.36	BU-RB610HDM	\$2.28
RB614HDM	6"	14T	Metal	3/4" x 6" x .035	5	\$2.36	BU-RB614HDM	\$2.28
RB618HDM	6"	18T	Metal	3/4" x 6" x .035	5	\$2.36	BU-RB618HDM	\$2.28
RB624HDM	6"	24T	Metal	3/4" x 6" x .035	5	\$2.36	BU-RB624HDM	\$2.28
RB810HDM	8"	10T	Metal 10/14 V.P.	3/4" x 8" x .035	5	\$3.67	BU-RB810HDM	\$3.52
RB814HDM	8"	14T	Metal	3/4" x 8" x .035	5	\$3.67	BU-RB814HDM	\$3.52
RB818HDM	8"	18T	Metal	3/4" x 8" x .035	5	\$3.67	BU-RB818HDM	\$3.52
RB1010HDM	10"	10T	Metal	3/4" x 10" x .035	5	\$5.35	BU-RB1010HDM	\$5.25
RB1018HDM	10"	18T	Metal	3/4" x 10" x .035	5	\$5.35	BU-RB1018HDM	\$5.25
RB1218HDM	12"	18T	Metal	3/4" x 12" x .035	5	\$5.55	BU-RB1218HDM	\$5.45
RB636DW	6"	6T	Drywall V Head	3/4" x 6" x .035	5	\$2.53	BU-RB636DW	\$2.44
R8CCRF	8"	Carbide Grit	Cast Iron-Ceramic Tile	3/4" x 8" x .050	1	\$9.03	BU-R8CCRF	\$8.89

MAIN OFFICE
 INTERNATIONAL TOOL MANUFACTURING
 71-08 51ST. AVENUE, WOODSIDE, NY 11377
 (718) 446-0711 - (800) 247-5696 - FAX (718) 899-6553



INTERNATIONAL TOOL MANUFACTURING
 675-E-PROGRESS CENTER AVE., LAWRENCEVILLE, GA 30043
 (770) 962-5454 - (800) 229-1776 - FAX (770) 962-5869

VIGOR™

Industrial Blades are Vigorous Blades.

- ◆ Made In U.S.A.
- ◆ 1/2" Universal Shank
- ◆ 45% Thicker Than All Purpose Blades
- ◆ Wider Than All Purpose Blades
- ◆ Stay Rigid
- ◆ No Vibration
- ◆ More Cuts Per Blade



Made In



VIGOR Heavy Duty Reciprocating Blades - Bi-Metal


Part #	Blade Length	Teeth Per Inch	Description	Width / Length	Pack QTY.	List	Bulk (50 Pcs.) Part #	List
VIHD61014	6"	10/14 V.P.	HEAVY DUTY	3/4" X 6" X .050	5	\$3.20	BU-VIHD61014	\$3.05
VIHD81014	8"	10/14 V.P.	HEAVY DUTY	3/4" X 8" X .050	5	\$4.38	BU-VIHD81014	\$4.18
VIHD12014	12"	10/14 V.P.	HEAVY DUTY	3/4" X 12" X .050	5	\$5.45	BU-VIHD12014	\$5.35

V.P. = Variable Pitch (Teeth)



VIGOR Demolition Reciprocating Blades - Bi-Metal

Part #	Blade Length	Teeth Per Inch	Description	Width / Length	Pack QTY.	List	Bulk (25 Pcs.) Part #	List
VIDM60006	6"	6T	DEMOLITION	7/8" X 6" X .062	3	\$5.83	BU-VIDM60006	\$5.76
VIDM60010	6"	10T	DEMOLITION	7/8" X 6" X .062	3	\$5.83	BU-VIDM60010	\$5.76
VIDM90006	9"	6T	DEMOLITION	7/8" X 9" X .062	3	\$8.15	BU-VIDM90006	\$7.75
VIDM90010	9"	10T	DEMOLITION	7/8" X 9" X .062	3	\$8.15	BU-VIDM90010	\$7.75
VIDM12006	12"	6T	DEMOLITION	7/8" X 12" X .062	3	\$9.84	BU-VIDM12006	\$9.35
VIHD12010	12"	10T	DEMOLITION	7/8" X 12" X .062	3	\$9.84	BU-VIHD12010	\$9.35



Tooth Style:



Standard beveled configuration



10/14 Variable Pitch beveled configuration

