

UQFB-200



Milbank 200 Ampere 2 Pole 240 Volt Bolt-on 10k Ampere Interrupting Capacity

SPECIFICATIONS

Brand Name	Milbank
Type	Current Interrupting Device
Special Features	Bolt On
Application	Metering Accessory
Standard	UL Listed
Voltage Rating	240 Volts Alternating Current
Amperage Rating	200 Ampere
Frequency Rating	60 Hertz
Phase	1 Phase
Frame	F-Frame
Trip Type	Thermal Magnetic
Interrupt Rating	10,000 Ampere Interrupting Capacity
Number Of Poles	2



Actuator	Lever
Connection	Lug to Lug
Auxiliary Contacts	No Auxiliary Contacts
Material	Non Metallic
Operating Temperature	40 Degrees Celsius
Height	7.438 IN
Length	3.281 IN
Width	3 IN

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

