



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
5.50"	10.50"	5.50"
<u>BP Height</u>	<u>BP Width</u>	
4.88"	10.13"	
<u>Hanging Weight</u>		
1.87 lb		

Lamping:

Incandescent MB	1,150 Rated Lumens
1.00 60W MB	Color Temperature
60 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
3.21 lb	8.25"	7.00"	12.50"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
19.27 lb	13.00"	15.75"	25.75"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
6.0000	783209031425	Yes	

Finish:

White WT

Glass:

Marble MR

Material:

Steel

Certification:

Dry Location
Location

Additional:

MB (Not Included)
Lighting Direction: Up