



# S9919

43T8/LED/96-850/BP 120-277V  
 43 watt T8 LED; Single pin base; 5000K; 50000 average rated hours; 5500 lumens

## Features

- Ballast by-pass - Double ended wiring
- No ballast or external driver required
- Direct wire 120-277V line voltage
- All glass tube
- Shatterproof coated - NSF approved
- 54W; 59W Fluorescent equivalency



S9919

Item Number	UPC	Voltage	Watts	Fluorescent Equivalent	Lamp Shape	Base	ANSI Base
S9919	045923099199	120-277	43	54W; 59W	T8	Single Pin	Fa8

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
43T8/LED/96-850/BP 120-277V	Non-Dimmable	White	96"	1.00"	5500	50000	5000

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification
Natural Light	82	210	10	Eggcrate	Yes	Yes	cULus - Damp Location Rated

Warranty
<a href="#">5 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

