

VERSAILLES COLLECTION

Versailles 3 Light Vanity Light Antique Pewter

45597AP (Antique Pewter)



Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Certifications/Qualifications

| | |
|--|------|
| Location Rating | Damp |
| www.kichler.com/warranty | |

Dimensions

| | |
|---|-------------|
| Base Backplate | 7.00 X 5.00 |
| Extension | 6.25" |
| Weight | 5.80 LBS |
| Height from center of Wall opening (Spec Sheet) | 6.75" |
| Height | 9.25" |
| Width | 23.00" |

Mounting/Installation

| | |
|--------------------------|------------|
| Install Glass Up or Down | Yes |
| Interior/Exterior | Interior |
| Mounting Style | Wall Mount |
| Mounting Weight | 2.50 LBS |

Primary Lamping

| | |
|------------------------|--------------|
| Lamp Included | Not Included |
| Lamp Type | A19 |
| Light Source | Incandescent |
| Max or Nominal Watt | 100W |
| # of Bulbs/LED Modules | 3 |
| Socket Type | Medium |
| Socket Wire | 150 |


Product/Ordering Information

| | |
|--------|--------------|
| SKU | 45597AP |
| Finish | Pewter |
| Style | Traditional |
| UPC | 783927522267 |

Specifications

| | |
|----------------------|-------------------------|
| Diffuser Description | Satin Ethced Cased Opal |
| Material | STEEL |

Additional Finishes

-  Antique Pewter
-  Olde Bronze

Kichler

7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010
Toll free: 866.558.5706 or kichler.com

Notes:

1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

