



GE
Lighting

75588 - GE LED Bright Stik™

LED9LS3/850

- ☞ GE's LED Bright Stik™ illuminates spaces instantly.
- ☞ Replaces 40-100 watt incandescent, halogen, and CFL
- ☞ User longer life, lower energy alternative to CFL - Last longer than CFL (15,000hrs)
- ☞ For example, using only 10 watts of energy, saves over \$82 in energy costs over the rated life of a lamp versus a standard 60-watt incandescent lamp based on \$0.11 per kWh.
- ☞ These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS.
- ☞ Worry-free use and disposal
- ☞ Energy Star Rated

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Dimmable	No
Primary Application	General Purpose
Product Color	White
Product Technology	LED
Rated Life (Hours)	15000 h
Dimmable / Non-Dimmable	No
Lamp Count	3
Life in Years	13.7 yr
Replacement Watts	60 W
Requested Structure	Carton
Estimated Energy Cost per Year	1.08
Base	E26
Bulb Shape	A19

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	800 lm
Color Rendering Index-CRI	80
Color Temperature	5000 K

PRODUCT INFORMATION

Product Code	75588
Description	LED9LS3/850
Alternative Unit Of Measure	EACH
Standard Package Quantity	16
Ean UPC	043168755887
Standard Package GTIN	00043168755887
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	16
Sales Unit	Each
UCC	
Alternative Unit Of Measure	CASE
Standard Package Quantity	16
Ean UPC	043168755887
Standard Package GTIN	10043168755884
No Of Items Per Sales Unit	
No Of Items Per Standard Package	16
Sales Unit	Case
UCC	

DIMENSIONS

Bulb Max Overall Length-MOL	4.45 mm
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Input Voltage [nom]	120 V
Rated power (Watts)	9 W