



7" Color Preference® Spin Light™

810 lm | 120VAC | Model 54690112 | Part SL-7-11-802-SV-N

- > Energy Saving 11.5 Watt Integrated LED
- > Uses 75% Less Energy than Equivalent 60 Watt Incandescent Bulb
- > Soft White 3000K CCT
Cool White 4000K CCT
Daylight 5000K CCT
- > Lasts 45.6 years or 50,000 Hours Continuous Use
- > Maintenance Free — No Bulb Replacements
- > 5 Year Limited Warranty
- > US Patent # 9500352, 9541270, D776326
- > CND Patent # 169113
- > Suitable for use in closets, as defined in NEC® Section 410.16



SPECIFICATIONS

Model	54690112
Part	SL-7-11-802-SV-N
Description	7" Color Preference® Spin Light
Input Voltage (VAC)	120
Wattage	11.5
Dimmability	Non-Dimmable
Average Rated Life ¹	50,000 hours
Typical Lumens ²	810
CCT ³	3000K/4000K/5000K
Location Rating	UL Damp
CRI ⁴	80
Beam Angle	120
Operating Temperature	Min -4°F (-20° C), Max 95°F (35° C)
Power Factor	>0.9
R9	15
DUV	-0.00247
Operating Frequency (Hz)	60

1 Hours lifetime with 70% lumen maintenance
 2 Thermally stable typical lumens (±10%)
 3 Thermally stable CCT (±10%)
 4 Color rendering index/Ra

LED lighting facts®
A Program of the U.S. DOE

Light Output (Lumens)	810
Watts	11.5
Lumens per Watt (Efficacy)	70.43
Color Accuracy Color Rendering Index (CRI)	80
Light Color Correlated Color Temperature (CCT)	3000 (Bright White)

Color scale: Warm White (2700K) | Bright White (3000K) | Daylight (4500K-6500K)

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: YN84-DRVTDC (5/5/2016)
 Model Number: 546901XX(XX=11-30)
 Type: Luminaire - Other

TO ORDER:
www.ETiSSL.com
 Call: 1.855.ETi.SSLI
 1.855.384.7754





7" Color Preference[®] Spin Light[™]

810 lm | 120VAC | Model 54690112 | Part SL-7-11-802-SV-N



SHIPPING INFORMATION

Model	54690112
Part	SL-7-11-802-SV-N
UPC	849489000848
Product Dimensions (W x H in.)	7 3/32 x 3 1/2
Product Dimensions (W x H cm.)	18 x 8.9
Product Weight (lbs.)	0.77
Inner Carton Quantity	N/A
Inner Carton Bar Code	N/A
Inner Carton Dimensions (L x W x H in.)	N/A
Inner Carton Dimensions (L x W x H cm.)	N/A
Inner Carton Weight (lbs)	N/A
Master Carton Quantity	5
Master Carton Bar Code	50849489000843
Master Carton Dimensions (L x W x H in.)	1' 8 33/64 x 7 29/32 x 8 17/64
Master Carton Dimensions (L x W x H cm.)	52.1 x 20.1 x 21..0
Master Carton Weight (lbs)	5.83
Pallet Quantity	300

AVAILABLE ACCESSORIES

Model	Description
95469011201	Diffuser Lens

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see www.etiled.us/fcc15b

TO ORDER:
www.ETiSSL.com
Call: 1.855.ETi.SSLI
1.855.384.7754

ETi Solid State Lighting, Inc.
720 Corporate Woods Parkway
Vernon Hills, IL 60061
Phone: 855.384.7754
Fax: 847.383.6256