



12" Low Profile Round Flushmount

14 Watts 1000lms LED 54436241

SPECIFICATIONS




ETI 14 watts 1000 lumen LED round flushmount fixture offers exceptional performance for precision lighting applications, while reducing energy and maintenance cost when compared with conventional light sources. Lasting over 10 times longer, these flushmount fixtures are high quality replacements for incandescent flushmount fixtures and is available in 4000K. They are UL listed for use in damp and dry locations. Warranty 5 years. Suitable for installations from 4° F to 95°F.

Designed to be used anywhere a standard incandescent fixture is used. Typically used in bedrooms, hallways, kitchens, living rooms and recreational rooms. Other applications apply in commercial, office, retail, restaurants, schools, hospitals and hotel/motel locations.

KEY FEATURES & BENEFITS

- 14 Watts
- Multi-volt 120-277V
- 1000 lumen, 4000K CCT
- Non-dimmable
- UL damp location rated
- No UV, IR or mercury
- Warranty for 5 years

FIXTURE DIMENSIONS



SKU# 54436241
Dimension A 11.4"
Dimension B 2.95"

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see www.etissl.com/fcc15b

www.etissl.com
855-384-7754



12" Low Profile Round Flushmount

14 Watts 1000lms LED 54436241

SPECIFICATION DATA

Item Number	Description	Watts	Input Voltage (VAC)	Average Rated Life ¹	Typical Lumens ²	CCT ³	CRI ⁴	Power Factor	R9	DUV	CBCP	Beam	Operating Frequency
54436241	12" Round Low Profile-MV, Non Dim	14	120-277	50,000 hours	1000	4000K	80	>0.98 @120V	14	0.0011	/	120	60Hz
¹ Hours lifetime with 70% lumen maintenance													
² Thermally stable typical lumens													
³ in compliance with ANSI C77.378 201X)													
⁴ Color rendering index/Ra													

SHIPPING INFORMATION

Item Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs) Dimensions (H x L x W)	Master Pack QTY	Master Carton Bar Code	Master Dimensions (H x L x W)	Master Pack Weight (lbs)
54436241	84948900 1241	11.4" x 11.4" x 2.95"	1.08	N/A	N/A	N/A	N/A	6	5084948900 1246	20.47" x 12.95" x 13.15"	10.8



The Americas Headquarters
720 Corporate Woods Parkway
Vernon Hills, IL 60061
855-384-7754
www.etissl.com



ETI

LED
lighting facts[®]
A Program of the U.S. DOE

Light Output (Lumens) **1000**
Watts **14**
Lumens per Watt (Efficacy) **71.43**

Color Accuracy **80**
Color Rendering Index (CRI)

Light Color **4000 (Bright White)**
Correlated Color Temperature (CCT)

Warm White Bright White Daylight

2700K 3000K 4500K 6500K

All results are according to IESNA LM-79-2005 - Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: YN84-A6QQ8D (1/21/2017)
 Model Number: 544362##(##-41-50)
 Type: Luminaire - Decorative