



S9859

9WPLV/LED/835/DR/4P
 9W LED PL 4-Pin; 3500K; 850 Lumens; G24q base; 50000
 Average rated hours; 120 Deg beam spread

Features

- Replaces 26, 32, and 42 watt CFLs
- Direct Replacement - for use with Electronic, Instant Start, Rapid Start, and Programmed Start ballasts with no rewiring required. Ballast required.
- Instant on to full brightness / no flickering
- Vertical operation
- Up to 70% energy saving
- Long life - 50,000 hours
- 5 year warranty

*Ballast required (See Ballast Compatibility Chart)

View:

[Ballast Compatibility Chart](#)

[Emergency Ballast Compatibility Chart](#)

This item has been discontinued.
 Possible replacement:

- [S29859](#)



S9859

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	Lamp Code	Dimmable/Non-Dimmable
S9859	045923098598	9	26, 32, and 42 watt CFL	PL	G24q	9WPLV/LED/835/DR/4P	Non-Dimmable
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
Frost	4-11/16"	1-15/16"	850	50000	3500	Neutral White	82
Beam Spread Deg	Operating Temperature	Package Type	CEC Status	DLC ID:	RoHS Compliant	UL or ETL Listed	UL Classification

120	-20C (-4F) to a maximum of +45C (+113F)	Box	Lawful for sale in California	PRDX2HQQ DLC Search	Yes	Yes	cULus Classified - Damp Location Rated
Warranty		Status		Suggested Substitute			
5 Year Limited		Discontinued		S29859			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

