

# FACADE FLOOD SERIES

Cat.#

Job

Type



**HUBBELL**  
Outdoor Lighting

Approvals

### APPLICATIONS

- Building facades, landscape lighting, sign lighting, display, as well as general safety and security lighting

### SPECIFICATIONS

- Durable die cast aluminum housing construction
- Polycarbonate door frame retains tempered glass and has twin tool-free latches for easy servicing. Gasketing provides weather-tight seal to housing
- Rugged 1/2" threaded knuckle mounting (1/2-10 NPSM)
- Wide uniform beam designed for close set backs. Lamp included
- Metal halide – HX-HPF -20°F starting  
Compact fluorescent – electronic ballast 50/60 Hz 120-277V
- Bronze powder paint finish


### LISTINGS

- Listed to UL1598 for use in wet locations

### PRODUCT IMAGE(S)



### DIMENSIONS




A	B	C	D	E	F	G
4 <sup>9</sup> / <sub>16</sub> "	6 <sup>7</sup> / <sub>8</sub> "	7 <sup>7</sup> / <sub>16</sub> "	8 <sup>1</sup> / <sub>16</sub> "	6 <sup>1</sup> / <sub>16</sub> "	2"	9"
116 mm	175 mm	189 mm	205 mm	154 mm	51 mm	229 mm

### LISTINGS



### ORDERING INFORMATION

ORDERING EXAMPLE: F-100H1



Catalog Number	Lamp Type/Wattage	NEMA Beam Type1 H° x V°	Voltage	Weight lbs. (kg)	EPA ft² (m²)	Ballast Type
<b>Pulse Start Metal Halide</b>						
<b>F-100H1</b>	100	6(128°) x 7(146°)	Quad-Tap®	10 (4.5)	.6 (0.1)	CWA
<b>Compact Fluorescent</b>						
<b>F-042F8†</b>	42	6H x 7V	Quad-Tap®	5 (2.3)	.6 (0.1)	ELECTRONIC

Note: All HPS units are NPF; Pulse Start Metal Halide units are all HPF  
 Note: Medium base lamps included  
 † CFL lamp is 3500K

### ACCESSORIES - Order Separately

Catalog Number	Description
<b>PBT-1</b>	Photocontrol, button type, 120V
<b>NMBC</b>	Non-metallic, high-impact phenolic weatherproof box and cover; Box is drilled at 180° for two burial cable connectors which are included allowing feed-through capability; gasketed cover has weathertight 1/2" hub; Brass cover screws
<b>S-302-M51</b>	Pole-top slipfitter for 1/2" knuckle, slipfits 2 3/8" OD pipe, bronze finish
<b>S-329-B</b>	Cast round box with (4) 1/2" side hubs and (1) 1/2" back hub - cover included with 1/2" hub for fixture knuckle; natural aluminum finish
<b>1031-3</b>	Spike with splice box and 6 ft. cordset, portable; gray finish

### REPLACEMENT PARTS


Catalog Number	Description
<b>FL214-FRAMEGLASS</b>	Lens door assembly
<b>FL214-GASKET</b>	Door gasket
<b>FL214-KNUCKLE</b>	Bronze 1/2" knuckle




S-302-M51




PBT-1



NMBC



S-329-B



1031-1




Hubbell Outdoor Lighting • 701 Millennium Boulevard • Greenville, SC 29607 • Phone: 864-678-1000

Due to our continued efforts to improve our products, product specifications are subject to change without notice.

© 2017 HUBBELL OUTDOOR LIGHTING, All Rights Reserved • For more information visit our website: [www.hubbelloutdoor.com](http://www.hubbelloutdoor.com) • Printed in USA

FACADE -SPEC 2/17

**PHOTOMETRICS** For additional photometric information and IES downloads, visit our web site at [www.hubbell-ltg.com](http://www.hubbell-ltg.com)



**FACADE FLOOD  
F100HX**

**PHOTOMETRIC REPORTS**

Catalog Number	Report #
F100H1	HP07474.IES



**HUBBELL**  
Outdoor Lighting

Hubbell Outdoor Lighting • 701 Millennium Boulevard • Greenville, SC 29607 • Phone: 864-678-1000  
Due to our continued efforts to improve our products, product specifications are subject to change without notice.

© 2017 HUBBELL OUTDOOR LIGHTING, All Rights Reserved • For more information visit our website: [www.hubbelloutdoor.com](http://www.hubbelloutdoor.com) • Printed in USA

**FACADE -SPEC 2/17**