

# 16" Low Profile Round Flushmount

22 Watts 1500lms LED 54437201

## SPECIFICATIONS




ETI 22 watts 1500 lumen LED round flushmount fixture offers exceptional performance for precision lighting applications, while reducing energy and maintenance cost when compared with conventional light sources. Lasting over 10 times longer, these flushmount fixtures are high quality replacements for incandescent flushmount fixtures and is available in 2700K. They are UL listed for use in damp and dry locations. Warranty 5 years. Suitable for installations from 4° F to 95°F.

Designed to be used anywhere a standard incandescent fixture is used. Typically used in bedrooms, hallways, kitchens, living rooms and recreational rooms. Other applications apply in commercial, office, retail, restaurants, schools, hospitals and hotel/motel locations.

### KEY FEATURES & BENEFITS

- 22 Watts
- Multi-volt 120-277V
- 1500 lumen, 2700K CCT
- Non-dimmable
- UL damp location rated
- No UV, IR or mercury
- Warranty for 5 years

### FIXTURE DIMENSIONS



SKU# 54437201  
Dimension A 15.4"  
Dimension B 2.95"

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see [www.etissl.com/fcc15b](http://www.etissl.com/fcc15b)

# 16" Low Profile Round Flushmount

22 Watt 1500lms LED 54437201

## SPECIFICATION DATA

Item Number	Description	Watts	Input Voltage (VAC)	Average Rated Life <sup>1</sup>	Typical Lumens <sup>2</sup>	CCT <sup>3</sup>	CRI <sup>4</sup>	Power Factor	R9	DUV	CBCP	Beam Angle	Operating Frequency
54437201	16" Round Low Profile-MV, Non Dim	22	120-277	50,000 hours	1500	2700K	80	>0.98 @120V	12	/	/	120	60Hz
<sup>1</sup> Hours lifetime with 70% lumen maintenance													
<sup>2</sup> Thermally stable typical lumens													
<sup>3</sup> in compliance with ANSI C77.378 201X													
<sup>4</sup> Color rendering index/Ra													

## SHIPPING INFORMATION

Item Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs) Dimensions (H x L x W)	Master Pack QTY	Master Carton Bar Code	Master Dimensions (H x L x W)	Master Pack Weight (lbs)
54437201	849489001258	15.4" x 15.4" x 2.95"	1.84	N/A	N/A	N/A	N/A	4	50849489001253	16.89" x 13.86" x 17.09"	11.9



The Americas Headquarters  
720 Corporate Woods Parkway  
Vernon Hills, IL 60061  
855-384-7754  
www.etissl.com



ETI

**LED lighting facts**  
A Program of the U.S. DOE

---

**Light Output (Lumens)** 1500  
**Watts** 22  
**Lumens per Watt (Efficacy)** 68.18

---

**Color Accuracy** 80  
Color Rendering Index (CRI)

---

**Light Color** 2700 (Warm White)  
Correlated Color Temperature (CCT)

2700K    3000K    Bright White    4500K    Daylight    6500K

---

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

**Visit [www.lightingfacts.com](http://www.lightingfacts.com) for the Label Reference Guide.**

Registration Number: YN84-JOBMV2 (1/21/2017)  
Model Number: 544372#/#(##=01-10)  
Type: Luminaire - Decorative