

3 Panel Rack Mount 1U Fiber Enclosure

Part Number: FE-18R-1U



RoHS
COMPLIANT



Dimensions

Depth	304.8 mm 12.0 in
Height	44.45 mm 1.75 in
Width	431.8 mm 17.0 in

Specification

Product Standard Certification	UL
RoHS 2002/95/EC	Compliant

Construction Materials

Material	16AWG Steel (Corrosion-Resistant)
Coating	Electrostatic Polyester Powder Coat

General Specifications

Mount Type	Rack Mount
Rack Units	1U
Panels	(3) Adapter Panel
Accommodates	(6-, 8-, 12- or 24- Fiber Panels)
24 Port Panels Only Available in LC Connectors	
Port Capacity	6-72
Doors	Front (Steel) 1/4" Turn Latch Rear - 1/4" Turn Latch
Includes	Labeling Kit For Ports Zip Ties & Installation Screws
Strain-relief Hardware	Routing Guides Maintain Min. Bend Radius
Weight (unloaded)	4.67 kg 10.3 lbs