



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker

**QBGFT2040**

**UPC:**786676026741

**Dimensions:**

- **Height:** 2 IN
- **Length:** 4.5 IN
- **Width:** 2.75 IN

**Weight:**.6 LB

**Notes:**HACR rated

**Warranties:**

- 1 year

**Specifications:**

- **Type:** Ground fault self test
- **Special Features:** 5 mA Trip Sensitivity
- **Amperage Rating:** 40A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Circuit Breaker Type:** QB
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on

**Supporting documents:**

- [Eaton Specification Sheet - QBGFT2040](#)

**Certifications:** No Data

**Product compliance:** No Data

