



S9855

9WPLH/LED/835/DR/2P
9W LED PL 2-Pin; 3500K; 850 Lumens; G24d base; 50000
Average rated hours; 120 Deg. beam spread; Type A; Ballast
dependent



S9855

Features

- Replaces 26 watt CFLs
- Direct Replacement - for use with Magnetic ballasts with no rewiring required. Ballast required.
- Instant on to full brightness / no flickering
- Horizontal operation
- Up to 70% energy saving
- Long life - 50,000 hours
- 5 year warranty

View:

[Ballast Compatibility Chart](#)
[Emergency Ballast Compatibility Chart](#)

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	Lamp Code	Dimmable/Non-Dimmable
S9855	045923098550	9	26 watt CFL	PL	G24d	9WPLH/LED/835/DR/2P	Non-Dimmable
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
Frost	6-5/8"	1-3/32"	850	50000	3500	Neutral White	82
Beam Spread Deg	Operating Temperature	Package Type	CEC Status	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty
120	-20C (-4F) to a maximum of +45C (+113F)	Box	Lawful for sale in California	Yes	Yes	cULus Classified - Damp Location Rated	5 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

