

## Straight Blade Devices

### 15A, 125V, 2 Pole, 3 Wire Grounding

HBL® Extra Heavy Duty Specification Grade Single Receptacle

# HUBBELL



#### Features

- One-piece brass integral ground strap
- Unique bypass contact design

#### Ordering Information

Description	Device Color	UPC	Catalog Number
Back and side wired	Brown	783585013855	HBL5261

#### Listings

UL Listed to UL498 File No. E2186  
Certified to CSA 22.2, No. 42 File 285  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

#### Specifications

Face	Nylon
Base	PBT
Power Contacts	.037 in. (.9) Brass
Ground Contact	Brass
Mounting Strap	.050" (1.3) Brass
Auto Self-grounding Clip	Stainless steel
Mounting Screws	Zinc plated steel

#### Performance

##### Electrical

Current Interrupting Certified for current interrupting at full rated current  
Dielectric Voltage Withstands 2,000V minimum

##### Mechanical


Product Identification Ratings are a permanent part of the device  
Terminal Accommodation #14-#10 AWG copper stranded or solid conductor only  
Terminal Identification Terminals identified in accordance with UL 498 and CSA

##### Environmental

Flammability Top: UL 94V-2, Base: UL 94V-0  
Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



15A 125V  
NEMA 5-15R  
UL CSA  
0.5 HP



#### Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions

#### Accessories

Wallplate or Weatherproof Cover

1.40" Opening

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

