



LED15WPT40KMED-G7



Description LED HID REPLACEMENT 15W-1875LM 4000K 80CRI
NON-DIM E26 UNIV BURN POS 100-277V

Ordering Code 09390

UNSPSC Code 39101628

Specifications

Voltage Rating	100~277
Voltage Type	AC
Watts	15
Lumens per Watt	125
Base Type	Medium Screw (E26)
MOL in/mm	5.75/146
MOD in/mm	2.52/64
Lumens	1875
CT deg K	4000
CRI	80+
Equivalent	50W HID
Ambient Operating Temp Range	-29° C (-20° F) to 60° C (140° F)
Approvals	cULus, RoHS Compliant

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335