

Lucian Collection
52 Inch Lucian LED Fan NI
 330000NI (Brushed Nickel)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____

Product Information


Product ID	330000NI
Finish	Brushed Nickel
Blade Finish	Silver/Walnut
Collection	Lucian Collection

Specifications

Number of Blades	5
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	52"
Blades Reversible	Yes
Blade Material	WOOD
Optional Blades Available	No
Downrod 1	1.00 OD X 4.00
Primary Control System	3 Speed Wall Control Limited Function
Remote Included	No
Wall Control Included	Yes
Low Ceiling Adaptable	No
Lead Wire Length	78.00"
Motor Size	172MM X 20MM
Motor Type	AC INDUCTION



Dimensions



Downrod	A	B	C	D
1.00 OD X 4.00	14.25	10.25	7.50	6.00

Downlight

Downlight Included	Yes
Light Source	LED
Downlight Bulb Included	Integrated
Downlight Bulb Type	LED
# of Bulbs/LED Modules	1
Watts	17 W
Initial Lumens	1600
Glass Description	Etched Cased Opal
Optional Light Kit Available	No
Efficacy (LMIW)	94
Kelvin Temperature	3000 K
Color Rendering Index	80

Safety Listings & Certifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Available Finishes

Lucian Collection
 52 Inch Lucian LED Fan NI
 330000NI (Brushed Nickel)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____

Finish	Fixture	Glass	Blade 1	Blade 2
Brushed Nickel	330000NI	ETCHED CASED OPAL	SILVER	WALNUT
Olde Bronze	330000OZ	ETCHED CASED OPAL	CHERRY	WALNUT

Installation

Installation requirements The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked ""For Fan Support""

Electrical Requirements 120V 60Hz AC

Hanging Weight 21.80 LBS

Minimum Distance Between Bottom Of Fan Blade To Floor 7 feet