

CRAFTMADE

Mobi - MOB6oOB

60" Ceiling Fan (Blades Sold Separately)

Finish: Oiled Bronze



The exquisite form of our Mobi fan almost makes you forget just how functional it can be. Producing superior air quality, this high-efficiency, three-blade fan with LED lighting is much more than beautiful home décor.


- Heavy Duty, 3-Speed Reversible Motor
- 4" and 6" Downrods (Included)
- Blades Sold Separately
- Integrated LED Light Source (Dimmable)
- Remote & Wall Control Included
- Dual Mount (Flat or Angled Ceiling)
- LED Module is Guaranteed for 3 years

Specs

Blade Sweep Opt (in.)	60
Blades	3
Blade Pitch (°)	Variable
Motor Size (MM)	188x15
Amps at High Speed	0.45
Watts (Hi Speed)	53.70
Energy Guide Watts	38
Energy Guide CFM	4063
Energy Guide CFM_Watts	106
High Speed (CFM)	5467.72
Carton Size (CU FT)	1.81
Bulb CCT	3000
Bulb Wattage	17
CRI	90
Light Kit Options	Integrated Light Kit
Lumens	1300

Dimensions

A:	16.33
A: (2° Downrod) -	13.59
B:	10.32
B: (2° downrod)	12.32
C:	8.03
D:	5.98
E:	8.85
F: w/o Light Kit -	8.85
Downrod Length (in.)	6
2° Downrod (in.)	4



Downloads

Mobi - MOB6oOB



[PDF Tear Sheet](#)



[Energy Guide](#)



[Energy Guide Image](#)

Craftmade • P.O. Box 1037 • Coppel, TX 75019 • [Privacy Policy](#) • [Site Map](#) • © 2018 All Rights Reserved